



## BIBD2/02, Double Sided Two Conductor Clear Insulated Multi-Tap Connector

By Burndy  
Catalog # BIBD2/02



Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 2 Sided Entry, 14-2/0 AWG, Al/Cu Rated.

### Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

### Application

For Indoor Use Only, Copper Or Stranded Aluminum

### General

Catalog Number	BIBD2/02
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	3/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Allen
Physical Attribute - Socket Size	0.19
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD, Multi-Port
UPC	781810223932
UPC 12 Digit	7818102239322

### Dimensions

Dimension - Height fraction	1.375 in
Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.52 in
Dimension - Width fraction	1-14/25 in
Dimension - Width inch	1.56 in
Dimension - Width mm	40 mm

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	8 AWG-2/0 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 Str
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Size	14-2/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li></ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity 1

## Product Assets

[3D Models - BIBD202\\_MODEL-IGES](#)

[3D Models - BIBD202\\_MODEL-STEP](#)

[3D Models - BIBD202\\_MODEL-PDF](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Catalogs - UNITAP™ Products](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR\\_BIBD\\_Lineart](#)

[Sales Drawings - sc210991-05](#)

[Specifications - BIBD2/02](#)

[Specifications - Burndy\\_BIBD202\\_Specsheet](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-BIBD202-SPEC-EN | REV 8/2024