

BIBD2/04, Double Sided Four Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBD2/04](#)



Aluminum Multiple Tap Connector, Clear Insulated, 4 Port, 2 Sided Entry, 14-2/0 AWG, Al/Cu Rated.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

General

Catalog Number	BIBD2/04
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	3/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	4
Physical Attribute - Number of Screws	4
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD, Multi-Port
UPC	781810223956
UPC 12 Digit	7818102239566

Dimensions

Dimension - Height fraction	1.375 in
Dimension - Height inch	1.38 in
Dimension - Height mm	35.1 mm
Dimension - L Length Overall mm	73 mm

Dimension - Length Overall inch	2.86 in
Dimension - Width fraction	1-14/25 in
Dimension - Width inch	1.56 in
Dimension - Width mm	40 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	8 AWG - 2/0 AWG
Conductor - Copper Str Size	#14;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 Str
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Size	14-2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

3D Models - BIBD204_MODEL-PDF

3D Models - BIBD204_MODEL-STEP

3D Models - BIBD204_MODEL-IGES

Catalogs - BURNDY Master Catalog - Section A - Mechanical

Catalogs - UNITAP™ Products

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_BIBD_Lineart

Sales Drawings - sc210991-05

Specifications - Burndy_BIBD204_Specsheet

Specifications - BIBD2/04



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BIBD204-SPEC-EN | REV 10/2024