

## BIBD2/04MT, Double Sided Mounted Four Conductor Clear Insulated Mult-Tap Connector

By Burndy

Catalog # [BIBD2/04MT](#)



Aluminum Multiple Tap Connector W/ Mount Holes, Clear Insulated, 4 Port, 2 Sided Entry, 14-2/0 Awg, Al/Cu Rated.

### Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

### Application

Clear Insulated Multiple Tap Connectors Single- and Double-Sided Entry with Mounting Holes

### General

Catalog Number	BIBD2/04MT
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	3/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	4
Physical Attribute - Number of Screws	6
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD-MT
UPC	781810253229
UPC 12 Digit	7818102532299

### Dimensions

Dimension - Height fraction	1.5 in
Dimension - Height inch	1.50 in
Dimension - Height mm	38.1 mm

Dimension - L Length Overall mm	107 mm
Dimension - Length Overall inch	4.20 in
Dimension - Width fraction	1-14/25 in
Dimension - Width inch	1.56 in
Dimension - Width mm	40 mm

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	8 AWG-2/0 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Size	14-2/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity 1

### Product Assets

3D Models - BIBD2-04MT\_MODEL-PDF  
3D Models - BIBD2-04MT\_MODEL-IGES  
3D Models - BIBD2-04MT\_MODEL-STEP  
Catalogs - BURNDY Master Catalog - Section A - Mechanical

Catalogs - UNITAP™ Products  
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog  
Customer Notices - Prop 65 Notice  
Interactive Catalog - BURNDY Full-Line Digital Catalog  
Product Cross Section Image(s) - BUR\_BIBD-MT\_LineArt  
Sales Drawings - SD213079-02\_B  
Specifications - BIBD2/04MT  
Specifications - BURNDY\_BIBD204MT\_Specsheet



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-BIBD204MT-SPEC-EN | REV 10/2024