

BIBD3504MT, Double Sided Mounted Four Conductor Clear Insulated Mult-Tap Connector

By Burndy
Catalog # BIBD3504MT



Mounting Version; Multi-Port; Double-Sided Entry.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

Clear Insulated Multiple Tap Connectors Single- and Double-Sided Entry with Mounting Holes

General

Catalog Number	BIBD3504MT
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	5/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	4
Physical Attribute - Number of Screws	6
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD-MT
UPC	781810253335
UPC 12 Digit	7818102533355

Dimensions

Dimension - Height fraction	2.625 in
Dimension - Height inch	2.63 in
Dimension - Height mm	66.8 mm
Dimension - L Length Overall mm	149 mm

Dimension - Length Overall inch	5.86 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Size Range	8 AWG-350 kcmil
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	10 AWG - 350 kcmil
Conductor Size	10 AWG-350 KCMIL
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - UNITAP™ Products](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_BIBD-MT_LineArt](#)

[Sales Drawings - SD213079-02_B](#)

[Specifications - BIBD3504MT](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BIBD3504MT-SPEC-EN | REV 10/2024