



# BIBD44FX, Double Sided Flex Rated Four Conductor Clear Insulated Mult-Tap Connector

By Burndy  
Catalog # BIBD44FX



Aluminum UNITAP, Double Sided Entry, #14-#4 Class B & C, #14-#6 Class G,H,I,K, DLO, 4 PORT.

## General

Connector Type	Multi Tap
Insulation	Y
Material	Aluminum
Number Of Ports	4
Plated	Y
Plating Type	Tin
Temperature Rating	-40° C to 135 °C
Trade Name	UNITAP™
UPC	621945439221
UPC 12 Digit	6219454392211

## Dimensions

Dimension - Length Overall inch	1.706 in
---------------------------------	----------

## Electrical Ratings

Amperage Rating	85 A
Voltage - Maximum	600 V

## Conductor Related

Conductor - AL Str Size Range	14 AWG-4 AWG
Conductor Size	14-4 AWG
Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - UNITAP™ Products](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50046931](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BIBD44FX-SPEC-EN | REV 1/2024