



# BIBD60010FX, Double Sided Flex Rated Ten Conductor Clear Insulated Multi-Tap Connector

By Burndy  
Catalog # [BIBD60010FX](#)



Aluminum UNITAP, Double Sided Entry, #4-600 Class B & C, #4-373 Class G,H,I,K, DLO, 10 PORT.

## General

Color Code	Green
Connector Type	Multi Tap
EU RoHS Indicator	Contact Manufacturer
Insulation	Y
Material	Aluminum
Number Of Ports	10
Plated	Y
Plating Type	Tin
Temperature Rating	-40° C to 135 °C
Trade Name	UNITAP™
UPC	621945438897
UPC 12 Digit	6219454388977

## Dimensions

Dimension - Length Overall inch	12.717 in
---------------------------------	-----------

## Electrical Ratings

Amperage Rating	420 A
Voltage - Maximum	600 V

## Conductor Related

Conductor - AL Str Size Range	4 AWG - 373 kcmil
Conductor Size	4 AWG-600 KCMIL
Conductor Type	<ul style="list-style-type: none"><li>AL C Str-Size</li><li>CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - UNITAP™ Products](#)  
[Sales Drawings - 50046931](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BIBD60010FX-SPEC-EN | REV 1/2024