

BIBD6006FXMT, Double Sided Mounted Flex Rated Six Conductor Clear Insulated Mult-Tap Connector



By Burndy
Catalog # [BIBD6006FXMT](#)

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

General

Catalog Number	BIBD6006FXMT
Color Code	Green
Connector Type	Multi Tap
Insulation	Y
Material	Aluminum
Number Of Ports	6
Plated	Y
Plating Type	Tin
Temperature Rating	-40° C to 135 °C
Trade Name	UNITAP™
UPC	621945440258
UPC 12 Digit	6219454402588

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Dimension - Length Overall inch	10.155 in
------------------------------------	-----------

Electrical Ratings

Amperage Rating	420 A
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Size Range	4 AWG - 373 kcmil
Conductor Size	4 AWG-600 KCMIL
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50050187](#)
- [Specifications - BIBD6006FXMT](#)