

BIBD75010, Double Sided Ten Conductor Clear Insulated Multi-Tap Connector

By Burndy

Catalog # [BIBD75010](#)



Aluminum Multiple Tap Connector, Clear Insulated, 10 Port, 2 Sided Entry, 2 AWG-750 kcmil, Al/Cu Rated.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

General

Catalog Number	BIBD75010
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	3/8
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	10
Physical Attribute - Number of Screws	10
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD, Multi-Port
UPC	781810232903
UPC 12 Digit	7818102329033

Dimensions

Dimension - Height fraction	3 in
Dimension - Height inch	3.00 in
Dimension - Height mm	76.2 mm
Dimension - L Length Overall mm	352 mm

Dimension - Length Overall inch 13.87 in

Dimension - Width fraction 3-19/50 in

Dimension - Width inch 3.38 in

Dimension - Width mm 86 mm

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - AL Str Size 2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil

Conductor - AL Str Size Range 2 AWG - 750 kcmil

Conductor - Copper Str Size 2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil

Conductor - Copper Str Size Range 2 AWG - 750 kcmil

Conductor Size 2 AWG-750 KCMIL

Conductor Type

- AL C Str-Size
- CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B

Standards - RoHS Compliance CM
Status
UL Listed No

Logistics

Minimum Pack Quantity 1

Product Assets

[3D Models - BIBD75010_MODEL-PDF](#)

[3D Models - BIBD75010_MODEL-IGES](#)
[3D Models - BIBD75010_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BIBD_Lineart](#)
[Sales Drawings - sc210991-09](#)
[Specifications - BIBD75010](#)



A Hubbell brand