

BIBD75010FX, Double Sided Flex Rated Ten Conductor Clear Insulated Mult-Tap Connector



By Burndy
Catalog # [BIBD75010FX](#)

Multiple Port Tap Double Sided Entry, 2 AWG-750 kcmil, 10 PORT.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

General

Catalog Number	BIBD75010FX
Color Code	Black
Connector Type	Multi Tap
Insulation	Y
Material	Aluminum
Number Of Ports	10
Plated	Y
Plating Type	Tin
Temperature Rating	-40° C to 135 °C
Trade Name	UNITAP™
UPC	621945439399
UPC 12 Digit	6219454393999

Dimensions

Dimension - Length Overall 13.625 in
inch

Electrical Ratings

Amperage Rating 475 A
Voltage - Maximum 600 V

Conductor Related

Conductor - AL Str Size Range 2 AWG-535 kcmil
Conductor Size 2 AWG-750 KCMIL
Conductor Type

- AL C Str-Size
- CU C Str-Size

Certifications And Compliance

Industry Standard(s) UL 486A-486B
Standards - Industry Standards UL 486A-486B
Met
Standards - RoHS Compliance CM
Status

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50046931](#)
[Specifications - BIBD75010FX](#)