




BIBD7505HD, Double Sided Heavy Duty Clear Insulated Five Conductor Mult-Tap Connector

By Burndy
Catalog # [BIBD7505HD](#)



750-2 TWO-SIDED 5 PORT HD CLR.

Application

For Indoor Use Only, Copper Or Stranded Aluminum

General

Catalog Number	BIBD7505HD
Connector Type	Multi Tap
Hex Key	3/8 in
Material	Aluminum
Material - Body	Tin Plated Aluminum
Material - Insulation	Plastisol
Material Type - Screw	Clear Coated Aluminum
Number Of Ports	5
Operating Temperature	-40°C TO 135°C.
UPC	621945480858

Dimensions

Length	6.75 in
Width	4.83 in

Electrical Ratings

Amperage Rating	535 A
Voltage - Maximum	600 V
Voltage Rating	600 V

Conductor Related

Conductor Size	2 AWG-750 KCMIL
Wire Size	#2 AWG TO 750 kcmil Class B, C

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50079817](#)
- [Specifications - BIBD7505HD](#)