

BIBS2/06FX, Single Sided Flex Rated Six Conductor Clear Insulated Mult-Tap Connector



By Burndy
Catalog # [BIBS2/06FX](#)

Aluminum UNITAP, Single Sided Entry, #14-2/0 Class B & C ,#14-
#1 Class G,H,I,K, DLO, 6 PORT.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

General

Catalog Number	BIBS2/06FX
Color Code	Black
Connector Type	Multi Tap
Insulation	Y
Material	Aluminum
Number Of Ports	6
Plated	Y
Plating Type	Tin
Temperature Rating	-40° C to 135 °C
Trade Name	UNITAP™
UPC	621945439542
UPC 12 Digit	6219454395422

Dimensions

Dimension - Height mm	0 mm
Dimension - Length Overall inch	3.954 in

Electrical Ratings

Amperage Rating	175 A
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Size Range	1 AWG - 14 AWG
Conductor Size	14-2/0 AWG
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50046931](#)
[Specifications - BURNDY_BIBS206FX_Specsheet](#)
[Specifications - BIBS2/06FX](#)