

# BIBS2/08, Single Sided Eight Conductor Clear Insulated Multi-Tap Connector

By Burndy  
Catalog # [BIBS2/08](#)



MULTI-PORT Single-Sided Entry.

## Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

## General

|                                       |               |
|---------------------------------------|---------------|
| Catalog Number                        | BIBS2/08      |
| Connector Type                        | Multi Tap     |
| Hex Key                               | 3/16          |
| Insulation                            | Y             |
| Insulation Type                       | Plastisol     |
| Material                              | Aluminum      |
| Number Of Ports                       | 8             |
| Physical Attribute - Number of Screws | 8             |
| Physical Attribute - Screw Type       | Allen         |
| Plated                                | N             |
| Plating Type                          | Unplated      |
| Temperature Rating                    | 194           |
| Trade Name                            | UNITAP™       |
| UPC                                   | 781810223925  |
| UPC 12 Digit                          | 7818102239255 |

## Dimensions

|                                 |             |
|---------------------------------|-------------|
| Dimension - Height inch         | 1.38 in     |
| Dimension - Height mm           | 35 mm       |
| Dimension - L Length Overall mm | 141 mm      |
| Dimension - Length Overall inch | 5.55 in     |
| Dimension - Width fraction      | 1-31/100 in |
| Dimension - Width inch          | 1.31 in     |
| Dimension - Width mm            | 33 mm       |

## Electrical Ratings

|                   |       |
|-------------------|-------|
| Operating Voltage | 600 V |
| Voltage - Maximum | 600 V |

## Conductor Related

|                                   |  |
|-----------------------------------|--|
| Conductor - AL Str Size Range     | 14 AWG - 2/0 AWG   |
| Conductor - Copper Str Size Range | 14 AWG - 2/0 AWG   |
| Conductor Size                    | 14-2/0 AWG   |
| Conductor Type                    | <ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul> |

## Certifications And Compliance

|   |              |
|---|--------------|
| Certification - CSA Approved            | Yes          |
| Certification - ETL                     | No           |
| Certification - UL Listed Direct Burial | No           |
| Certification - UL Recognized           | No           |
| Certification - cULus                   | No           |
| Industry Standard(s)                    | UL 486A-486B |
| Standards - Industry Standards Met      | UL 486A-486B |
| Standards - RoHS Compliance             | CM           |
| Status                                  |              |
| UL Listed                               | Yes          |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_BIBS\\_Lineart](#)
- [Sales Drawings - sc210991-11](#)
- [Specifications - BIBS2/08](#)
- [Specifications - BURNDY\\_BIBS208\\_Specsheet](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-BIBS208-SPEC-EN | REV 10/2024