

# BIBS2/08MT, Single Sided Mounted Eight Conductor Clear Insulated Multi-Tap Connector



By Burndy  
Catalog # [BIBS2/08MT](#)

Mounting Version; Multi-Port Single-Sided Entry.

## Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

## General

Catalog Number	BIBS2/08MT
Connector Type	Multi Tap
Hex Key	3/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	8
Physical Attribute - Number of Screws	10
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	UNITAP™
UPC	781810252888
UPC 12 Digit	7818102528888

## Dimensions

Dimension - Height inch	1.50 in
Dimension - Height mm	35 mm
Dimension - L Length Overall mm	175 mm
Dimension - Length Overall inch	6.89 in
Dimension - Width fraction	1-31/100 in

Dimension - Width inch	1.25 in
Dimension - Width mm	32 mm

## Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

## Conductor Related

Conductor - AL Str Size Range	14 AWG - 2/0 AWG
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Size	14-2/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467 Met

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_BIBS-MT\\_LineArt](#)
- [Sales Drawings - 213079](#)
- [Specifications - BURNDY\\_BIBS208MT\\_Specsheet](#)
- [Specifications - BIBS2/08MT](#)