



# BIBS3503, Single Sided Three Conductor Clear Insulated Multi-Tap Connector

By Burndy  
Catalog # BIBS3503



Aluminum Multiple Tap Connector, Clear Insulated, 3 Port, 1 Sided Entry, 10 AWG-350 kcmil, Al/Cu Rated.

## Application

For Indoor Use Only, Copper Or Stranded Aluminum

## General

Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	5/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	3
Physical Attribute - Number of Screws	10
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810131770
UPC 12 Digit	7818101317700

## Dimensions

Dimension - Height inch	2.50 in
Dimension - L Length Overall mm	80 mm
Dimension - Length Overall inch	3.13 in
Dimension - Width inch	2.32 in
Dimension - Width mm	59 mm

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - AL Str Size Range	10 - 350 Str
Conductor - Copper Str Size Range	10 AWG - 350 kcmil
Conductor Size	10 AWG-350 KCMIL
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [3D Models - BIBS3503\\_MODEL-STEP](#)
- [3D Models - BIBS3503\\_MODEL-IGES](#)
- [3D Models - BIBS3503\\_MODEL-PDF](#)
- [Catalogs - UNITAP™ Products](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - sc210991-13](#)



A proud member of the Hubbell Family.

