



BIBS3506DB, Direct Burial Submersible Six Conductor Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBS3506DB](#)



Direct Burial UNITAP™, 350 Kcmil -12 AWG Str., 7.45 in L, Designed specifically for direct burial applications.

Application

For Outside Direct Burial

General

Connector Type	Multi Tap
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	450 LBS/in
Insulation	Y
Material	Aluminum
Number Of Ports	6
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port - Direct Burial
UPC	781810523629
UPC 12 Digit	7818105236299

Dimensions

Dimension - Height inch	2.46 in
Dimension - L Length Overall mm	189 mm
Dimension - Length Overall inch	7.45 in
Dimension - Strip Length inch	1.125
Dimension - Width inch	4.06 in
Dimension - Width mm	103 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size Range	12 - 350 Str
Conductor - Copper Str Size Range	12 AWG - 350 kcmil
Conductor Size	12 AWG-350 KCMIL
Conductor Type	<ul style="list-style-type: none">AL C Str-SizeCU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - BIBS3506DB_MODEL-IGES](#)
[3D Models - BIBS3506DB_MODEL-PDF](#)
[3D Models - BIBS3506DB_MODEL-STEP](#)
[Catalogs - UNITAP™ Products](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 30013013](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BIBS3506DB-SPEC-EN | REV 1/2024