

BIBS5003DB, Direct Burial Submersible Three Conductor Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBS5003DB](#)



Multi Port Direct Burial, 3 Ports, 500 kcmil-12 AWG Str, 600 V.

Application

For Outside Direct Burial

General

Catalog Number	BIBS5003DB
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Installation Torque	550 LBS/in
Recommended in-lb	
Insulation	Y
Material	Aluminum
Number Of Ports	3
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port - Direct Burial
UPC	781810523636
UPC 12 Digit	7818105236366

Dimensions

Dimension - Height inch	3.13 in
Dimension - L Length Overall mm	109 mm
Dimension - Length Overall inch	4.31 in
Dimension - Strip Length inch	1.5
Dimension - Width inch	4.58 in
Dimension - Width mm	116 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Size Range	12 AWG - 500 kcmil
Conductor - Copper Str Size Range	12 AWG - 500 kcmil
Conductor Size	12 AWG-500 KCMIL
Conductor Type	<ul style="list-style-type: none"> AL C Str-Size CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BIBS_Lineart](#)
- [Sales Drawings - 30013660](#)
- [Specifications - BIBS5003DB](#)