

BIBS60012, Single Sided Twelve Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBS60012](#)



MULTI-PORT Single-Sided Entry.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

General

| | |
|--|---------------|
| Catalog Number | BIBS60012 |
| Connector Type | Multi Tap |
| Hex Key | 3/8 |
| Insulation | Y |
| Insulation Type | Plastisol |
| Material | Aluminum |
| Number Of Ports | 12 |
| Physical Attribute - Number of Screws | 12 |
| Physical Attribute - Screw Type Plated | Allen N |
| Plating Type | Unplated |
| Temperature Rating | 194 |
| Trade Name | UNITAP™ |
| UPC | 781810233047 |
| UPC 12 Digit | 7818102330477 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - Height inch | 2.75 in |
| Dimension - L Length Overall mm | 394 mm |
| Dimension - Length Overall inch | 15.53 in |
| Dimension - Width inch | 2.38 in |
| Dimension - Width mm | 60 mm |

Electrical Ratings

| | |
|-------------------|-------|
| Operating Voltage | 600 V |
| Voltage - Maximum | 600 V |

Conductor Related

| | |
|-----------------------------------|--|
| Conductor - AL Str Size Range | 4 AWG - 600 kcmil |
| Conductor - Copper Str Size Range | 4 AWG - 600 kcmil |
| Conductor Size | 4 AWG-600 KCMIL |
| Conductor Type | <ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size |

Certifications And Compliance

| | |
|---|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 5 |
|-----------------------|---|

Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BIBS_Lineart](#)
- [Sales Drawings - sc210991-14](#)
- [Specifications - BIBS60012](#)



A Hubbell brand