

BIBS7508, Single Sided Eight Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBS7508](#)



Aluminum Multiple Tap Connector, Clear Insulated, 8 Port, 1 Sided Entry, 2 AWG-750 kcmil, Al/Cu Rated

Features

- Clear Platisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear platisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

General

Catalog Number	BIBS7508
Connector Type	Multi Tap
EU RoHS Indicator	Contact Manufacturer
Hex Key	3/8
Insulation	Y
Insulation Type	Platisol
Material	Aluminum
Number Of Ports	8
Physical Attribute - Number of Screws	8
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS
UPC	781810233092
UPC 12 Digit	7818102330922

Dimensions

Dimension - Height inch	3.00 in
Dimension - Height mm	76 mm
Dimension - L Length Overall mm	276 mm
Dimension - Length Overall inch	10.88 in
Dimension - Width inch	2.70 in
Dimension - Width mm	69 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Size Range	2 AWG - 750 kcmil
Conductor - Copper Str Size Range	2 AWG - 750 kcmil
Conductor Size	2 AWG-750 KCMIL
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BIBS_Lineart](#)
- [Sales Drawings - sc210991-15](#)
- [Specifications - BIBS7508](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BIBS7508-SPEC-EN | REV 10/2024