



BITO2/0FX, Opposite Side Flex Rated Two Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BITO2/0FX](#)



Insulated tap offset ports flex conductor rated, Wire size: 2/0,
Color: Black, Amp Rating : 175.

Features

- Type BIT-FX and BITO-FX Multi-tap connectors are quickly and easily installed
- UL486B Listed, Dual rated AL9CUFor stranded copper or stranded aluminum applications

Application

Clear Insulated Multiple Tap Connectors

General

Color Code	Black
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	3/16 in
Insulation	Y
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNITAP
Temperature Rating	135°C
Trade Name	UNITAP™
Type	BIT, UNITAP
UPC	621945440647
UPC 12 Digit	6219454406477

Dimensions

Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	38.61 mm
Dimension - Length Overall inch	1.52 in
Dimension - Width inch	1.56 in
Dimension - Width mm	39.62 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Size Range	14 AWG - 2/0 AWG
Conductor - Copper DLO Size Range	14 str.-1 str.
Conductor - Copper Flex G Size Range	14 str.-1 str.
Conductor - Copper Flex H Size Range	14 str.-1 str.
Conductor - Copper Flex I Size Range	14 str.-1 str.
Conductor - Copper Flex K Size Range	14 str.-1 str.
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Size	14-2/0 AWG
Conductor Type	<ul style="list-style-type: none">AL C Str-SizeCU C Str-SizeCU C Flex-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50046931](#)





A proud member of the Hubbell Family.