



BS16, Vinyl Splice, #22-16 AWG

By Burndy
Catalog # [BS16](#)

Vinyl Splice For 22 - 16 AWG.



Features

- Manufactured from seamless electrolytic copper tubing to provide maximum conductivity and tensile strength in a high quality design with no seams to split
- Funnel entry for easy wire insertion
- Electro-tin plating provides durable, long lasting resistance to corrosion
- Expanded insulation support to lower inventory requirements
- Vinyl insulation provides an economical means of providing high dielectric values and cable insulation support

Application

For Accommodating A Broad Range Of 600 Volt Cables

General

Catalog Number	BS16
Color Code	Red
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	VINYLINK
Temperature Rating	105
Trade Name	VINYLINK™
Type	BS
UPC	781810805169
UPC 12 Digit	7818108051699

Dimensions

Dimension - Diameter Max Size	0.145 in
inch	
Dimension - Length Overall	1.00 in
inch	
Dimension - Outside Diameter	0.145 in
inch	
Dimension - Strip Length	1/4 in
inch	

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size Range	20 -16 AWG
Conductor - Copper Str Size Range	20 AWG-16 AWG
Conductor Size	22 - 16 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[3D Models - BS16_MODEL-IGES](#)
[3D Models - BS16_MODEL-PDF](#)
[3D Models - BS16_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KTFBS_LineArt](#)
[Sales Drawings - 50094190](#)
[Specifications - BS16](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BS16-SPEC-EN | REV 8/2024