



## BSD2050N, Static Discharge Reel, Heavy Duty, Cable Length: 50' (Nylon Covered)

By Burndy

Catalog # BSD2050N

Static Discharge Reels, Heavy Duty, Cable Length: 50 Feet (Nylon Covered), Weight: 12 LB.



### Features

- 50 foot cable length
- Automatic E-Z PULL Rewinding
- Rugged Steel Construction
- Compact Enclosed Design
- Positive Ratchet Lock with Ratchet On/Off Switch
- Steel Cable Installed
- 100 Amp Universal Jaw-Type Grounding Clamp
- Red Baked-on Finish

### Application

Used to dissipate static charge build-up developed while filling or dispensing fuel or other combustible liquids from fuel trucks or rail cars

### General

Cable Length	50 ft
Cable Lock	Y
Cable Type	Aircraft Steel
Catalog Number	BSD2050N
Color - Housing	Red
EU RoHS Indicator	Contact Manufacturer
Material	Copper
Material Type - Outer Shell	Nylon
Physical Attribute - Number of Clamping Elements	1
Plated	N
Plating Type	Unplated
Sub Brand	REEL
Tension	Adjustable
Type	Static Discharge Reel
UPC	781810504475
UPC 12 Digit	7818105044755

### Dimensions

Cable Length Active	600
Dimension - Height inch	8.8 in
Dimension - L Length Overall mm	219 mm
Dimension - Length Overall inch	8.6 in
Dimension - Width inch	3.40 in
Dimension - Width mm	86 mm

### Conductor Related

Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>
----------------	---

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_BSD2050\\_LineArt](#)
- [Sales Drawings - 30003968](#)
- [Specifications - BSD2050N](#)