



BSD2050Y, Static Discharge Reel, Heavy Duty, Cable Length: 35' plus 15' for Y

By Burndy
Catalog # [BSD2050Y](#)



Static Discharge Reels, Heavy Duty, Cable Length: 35 Feet Plus 15 FT for Y.

Features

- 35 foot cable length plus 15 foot for Y
- Automatic E-Z PULL Rewinding
- Rugged Steel Construction
- Compact Enclosed Design
- Positive Ratchet Lock with Ratchet On/Off Switch
- Steel Cable Installed
- 100 Amp Universal Jaw-Type Grounding Clamp
- Red Baked-on Finish

General

| | |
|--|----------------|
| Cable Length | 50 ft |
| Cable Lock | Y |
| Cable Type | Aircraft Steel |
| Catalog Number | BSD2050Y |
| Color - Housing | Red |
| Material | Copper |
| Physical Attribute - Number of Clamping Elements | 2 |
| Plated | N |
| Plating Type | Unplated |
| Tension | Adjustable |
| UPC | 781810504482 |
| UPC 12 Digit | 7818105044822 |

Dimensions

| | |
|---------------------------------|---------|
| Cable Length Active | 600 |
| Dimension - Height inch | 8.80 in |
| Dimension - Length Overall inch | 8.60 in |
| Dimension - Width inch | 3.40 in |
| Dimension - Width mm | 86 mm |

Conductor Related

| | |
|----------------|---|
| Conductor Type | <ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size |
|----------------|---|

Certifications And Compliance

| | |
|------------------------------|----|
| Certification - CSA Approved | No |
|------------------------------|----|

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

- [3D Models - BSD2050Y_MODEL-STEP](#)
- [3D Models - BSD2050Y_MODEL-PDF](#)
- [3D Models - BSD2050Y_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BSD2050_LineArt](#)
- [Sales Drawings - 30003968](#)
- [Specifications - BSD2050Y](#)