

# Torque Wrench, 3/8" Drive, 150-750 IN LB

By Burndy Catalog # BTW150750

Torque Wrench, 3/8" Drive, 150-750 IN LB.



- Quick Release button
- Simple torque selection using Spring-Loaded Lock Ring
- Easy to read Laser marked scale
- 3-Way direction switch
- Knurled metal handle
- Wrench produces audible click when selected torque is reached.

### Application

Torque

## General

Application - For Use On

EU RoHS Indicator Installation Torque Recommended in-Ib Torque Range Type UPC UPC 12 Digit Use with any mechanincal connection with torque values within range of specific torque wrench Yes 150-750 in-Ib

150-750 in-lb Torque Wrench 781810535424 7818105354244



## Dimensions

Length

16 in

1

#### **Certifications and Compliance**

Industry Standard(s)

Standards - Industry Standards Met

Standards - RoHS Compliance EX Status

#### Logistics

Minimum Pack Quantity Package Contents

Torque Wrench, 3/8" Drive, 150-750 IN LB

• ASME B107.14-2004

• ASME B107.14M-2004

• ISO 6789:2003

• ISO 6789

## **Product Assets**

Catalogs - Full Line BURNDY Catalog Sales Drawings - 30019829



©2024 Hubbell Incorporated. All rights reserved. BRDY-BTW150750-SPEC-EN | REV 1/2024