



BYNA325MM2T15UHACC, Terminal Pad Assembly for ACCC, Undrilled with TMH24 Hardware Kit, 352mm-380mm ACCC, 15 Degree, 230kV



By Burndy
Catalog # [BYNA325MM2T15UHACC](#)

HYLUG™ Terminal Pad Assembly (ACCC) Undrilled with TMH24 Hardware Kit, 352mm²-380mm² ACCC, 15°, 230kV.

General

Catalog Number	BYNA325MM2T15UHACC
Connector Type	Terminal
Installation Torque	300 in-lb
Recommended in-lb	
Trade Name	HYLUG™
UPC	781810510780
UPC 12 Digit	7818105107800

Dimensions

Dimension - Inside Diameter inch	0.97 in
Dimension - Outside Diameter inch	1.14 in
Physical Attribute - Tongue Angle	15 Degree

Conductor Related

Conductor - ACCC Str Size	325 kcmil(Lisbon);330mm ² (Oslo);380mm ² (Amsterdam)
Conductor - ACCC Str Size Range	325mm ² (Lisbon)-380mm ² (Amsterdam)

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - BYNA325MM2T15UHACC_MODEL-IGES](#)
- [3D Models - BYNA325MM2T15UHACC_MODEL-PDF](#)
- [3D Models - BYNA325MM2T15UHACC_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50044936](#)
- [Specifications - BYNA325MM2T15UHACC](#)