

# BYNA32RT15HACCC, Terminal Pad Assembly, TMH24 Hardware Kit, 230mm, 15 Degree



By Burndy  
 Catalog # [BYNA32RT15HACCC](#)

HYLUG™ Terminal Pad Assembly (ACCC) with TMH24 Hardware Kit, 230mm² ACCC, 15°, 230kV.

## General

Catalog Number	BYNA32RT15HACCC
Connector Type	Terminal
Installation Torque	300 in-lb
Recommended in-lb	
Material	Aluminum
Trade Name	HYLUG™
UPC	781810474570
UPC 12 Digit	7818104745700

## Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	0.80 in
Dimension - L Length Overall mm	393 mm
Dimension - Length Overall inch	15.5 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	3.25 in
Physical Attribute - Tongue Angle	15 Degree

## Conductor Related

Conductor - ACCC Str Size	230mm2(Copenhagen)
Conductor - ACCC Str Size Range	230mm2(Copenhagen)

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

## Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_ACCC Deadend fig\\_1](#)
- [Sales Drawings - 50068174](#)
- [Specifications - BYNA32RT15HACCC](#)