



BYNA32RT15HHT, 300 kcmil-336.4 kcmil, ACSS Lug

By Burndy
Catalog # [BYNA32RT15HHT](#)



300 kcmil -336.4 kcmil ACSS Hylug.

General

Catalog Number	BYNA32RT15HHT
Connector Type	Terminal
Die Index	717
Feature - Barrel Style	Tapered
Feature - Barrel Type	Long
Installation Torque	300 in-lb
Recommended in-lb	
Material	Aluminum Alloy
Physical Attribute - Number of Holes	4
Trade Name	HYLUG™
UPC	781810514078
UPC 12 Digit	7818105140788

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	4.5 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	416 mm
Dimension - Length Overall inch	16.41 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	3.25 in

Physical Attribute - Tongue Angle 15 Degree

Conductor Related

Conductor Range 300-336.4 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10092588](#)
[Specifications - BUNA32RT15HHT](#)