



BYNA36R15HHT, Single Pad Full Tension Compression Deadend, Standard 15 Degree NEMA Pad, includes Hardware, for ACSS Conductor



By Burndy
Catalog # [BYNA36R15HHT](#)

BURNDY; HYLUG; BYNA-R-HHT, Kit; Features: Single pad Full tension compression deadend for 250 Deg C rated ACSS transmission lines up to and including 230kV; Standard 15 Deg NEMA tap pad provides either 0 Deg or 30 Deg tap when BYNA-R15 terminal is used; with Hardware; For ACSS Conductor; RoHS Compatible.

General

Catalog Number	BYNA36R15HHT
Connector Type	Terminal
Trade Name	HYLUG™
UPC	781810487822
UPC 12 Digit	7818104878222

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10113639](#)
- [Specifications - BYNA36R15HHT](#)