

BYNA36RT15ACCC, Terminal Pad Assembly for ACCC, 285mm, 15 Degree Pad, 230kV



By Burndy
Catalog # [BYNA36RT15ACCC](#)

HYLUG™ Terminal Pad Assembly (ACCC), 285mm² ACCC, 15°, 230kV.

General

Catalog Number	BYNA36RT15ACCC
Connector Type	Terminal
Die Index	720
Installation Torque	300 in-lb
Recommended in-lb	
Material	Aluminum
Trade Name	HYLUG™
UPC	781810480861
UPC 12 Digit	7818104808611

Dimensions

Dimension - D inch	4.25 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	0.92 in
Dimension - L Length Overall mm	402 mm
Dimension - Length Overall inch	15.8 in
Dimension - Outside Diameter inch	1.41 in
Dimension - Pad Width inch	3.25 in
Physical Attribute - Tongue Angle	15 Degree

Conductor Related

Conductor - ACCC Str Size	285mm ² (Casablanca)
Conductor - ACCC Str Size Range	285mm ² (Casablanca)

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

Product Assets

- [3D Models - BYNA36RT15ACCC_MODEL-PDF](#)
- [3D Models - BYNA36RT15ACCC_MODEL-IGES](#)
- [3D Models - BYNA36RT15ACCC_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50064993](#)
- [Specifications - BYNA36RT15ACCC](#)