



# BYNA39RT15HT, Compression Terminal, ACSS 556.5 kcmil, 15 Degree Pad, High Temperature



By Burndy  
Catalog # [BYNA39RT15HT](#)

BURNDY; HYLUG; BYNA-RT15HT, EHV; Features: 15 Deg Compression terminal for 250 Deg C ACSS transmission lines at 345 kV and over; For ACSS Conductor; RoHS Under Investigation; Conductor Range (Main/Primary): 556.5 KCMIL ACSS.

## General

Catalog Number	BYNA39RT15HT
Connector Type	Terminal
UPC	781810493458
UPC 12 Digit	7818104934588

## Dimensions

Dimension - D inch	4.50 in
Dimension - Length Overall inch	17.12 in
Dimension - Pad Width inch	3.25 in

## Conductor Related

Conductor - ACSS Str Size	556.5 (24/7) kcmil;556.5 (26/7)kcmil
---------------------------	--------------------------------------

Conductor - ACSS Str Size Range	556.5 (24/7) kcmil-556.5 (26/7)kcmil
---------------------------------	--------------------------------------

## Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10092588](#)
- [Specifications - BYNA39RT15HT](#)