



BYNA451R15HT, Compression Terminal for ACSS, 15 Degree

By Burndy
Catalog # [BYNA451R15HT](#)



BURNDY; HYLUG; BYNA-R15HT; Features: 15 Deg Compression terminal for ACSS transmission lines up to and including 230 kV; For ACSS Conductor; RoHS Under Investigation.

General

Connector Type	Terminal
Material	Aluminum
Physical Attribute - Number of Holes	4
UPC	781810497432
UPC 12 Digit	7818104974322

Dimensions

Dimension - D inch	3.95 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size fraction	14/25
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	15.10 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.8 in
Dimension - Pad Width inch	3.22 in

Conductor Related

Conductor - ACSS Str Size	715.5 (24/7) kcmil;715.5 (26/7) kcmil;715.5 (30/19) kcmil;795 (42/7) kcmil;795 (20/7) kcmil;795 (45/7) kcmil;795 (22/7) kcmil;795 (24/7) kcmil;795 (54/7) kcmil;795 (26/7) kcmil;795 (30/19) kcmil
Conductor - ACSS Str Size Range	715.5 (24/7) kcmil-795 (30/19) kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10113639](#)



A proud member of the Hubbell Family.