

# BYNA451RTHT, ACSS - Compression Terminal

By Burndy  
Catalog # [BYNA451RTHT](#)



BURNDY; HYLUG; BYNA-RTHT, EHV; Features: Straight Compression terminal for 250 DegC ACSS transmission lines at 345 kV and over; For ACSS Conductor; RoHS Under Investigation.

## General

Catalog Number	BYNA451RTHT
Connector Type	Terminal
Feature - Barrel Style	Tapered
Feature - Barrel Type	Long
Material	Aluminum
Physical Attribute - Number of Holes	4
UPC	781810514399
UPC 12 Digit	7818105143999

## Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.95 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	15.46 in
Dimension - N inch	1.12 in
Dimension - Outside Diameter inch	1.8 in
Dimension - Pad Width inch	3.22 in
Dimension - Thread Size	1/2
Physical Attribute - Tongue Angle	Straight

## Conductor Related

Conductor - ACSS Str Size	715.5 (26/7) kcmil
Conductor - ACSS Str Size Range	715.5 (26/7) kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	384

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10113638](#)
- [Specifications - BYNA451RTHT](#)