



BYNA49R15HT, Compression Terminal for 1033.5 ACSS, 15 Degree NEMA Tap Pad



By Burndy
Catalog # [BYNA49R15HT](#)

BURNDY; HYLUG; BYNA-R15HT; Features: 15 Deg Compression terminal for ACSS transmission lines up to and including 230 kV; For ACSS Conductor; RoHS Under Investigation.

General

Catalog Number	BYNA49R15HT
Connector Type	Terminal
UPC	781810495742
UPC 12 Digit	7818104957422

Dimensions

Dimension - D inch	3.95 in
Dimension - Length Overall inch	15.14 in
Dimension - Pad Width inch	3.22 in

Conductor Related

Conductor - ACSS Str Size	900(45/7) kcmil;1113(45/7) kcmil
---------------------------	----------------------------------

Conductor - ACSS Str Size Range	900(45/7) kcmil-1113(45/7) kcmil
---------------------------------	----------------------------------

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10113639](#)
- [Specifications - BYNA49R15HT](#)