

BYNA49RHT, Compression Terminal, Straight for ACSS Conductor

By Burndy
Catalog # [BYNA49RHT](#)



BURNDY; HYLUG; BYNA-RHT; Features: Straight Compression terminal for ACSS transmission lines up to and including 230 kV; For ACSS Conductor; RoHS Under Investigation.

General

Catalog Number	BYNA49RHT
Connector Type	Terminal
Die Index	727
Feature - Barrel Style	Tapered
Feature - Barrel Type	Long
Material	Aluminum
Physical Attribute - Number of Holes	4
UPC	781810514405
UPC 12 Digit	7818105144055

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.95 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	15.66 in
Dimension - N inch	1.12 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Pad Width inch	3.22 in
Dimension - Thread Size	1/2
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACSS Str Size	900 (45/7) kcmil;900 (54/7) kcmil;954 (42/7) kcmil;954 (20/7) kcmil;954 (45/7) kcmil;954 (48/7) kcmil;954 (24/7) kcmil;954 (54/7) kcmil;954 (30/19) kcmil;1033.5 (42/7) kcmil;1033.5 (45/7) kcmil;1033.5 (48/7) kcmil;1033.5 (54/7) kcmil;1113 (42/7) kcmil;1113 (45/7) kcmil;1113 (48/7) kcmil;1113 (54/19) kcmil
Conductor - ACSS Str Size Range	900 (45/7) kcmil-1113 (54/19) kcmil

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section I - Transmission Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10113640](#)
[Specifications - BYNA49RHT](#)