



BYNA49RT15HHT, Compression Deadend, includes Hardware, Cardinal 1222 ACSS



By Burndy
Catalog # [BYNA49RT15HHT](#)

BURNDY; HYLUG; BYNA-RT-HHT, EHV; Features: Terminal and hardware; Full tension compression deadend for 250 Deg C rated ACSS transmission lines at 345 kV and over; 15 Deg NEMA Tap Pad Terminal; For ACSS Conductor; RoHS Compatible; Conductor Range (Main/Primary): 900 - 1113 KCMIL (45-7 Str) ACSS.

General

Catalog Number	BYNA49RT15HHT
Connector Type	Terminal
Trade Name	HYLUG™
UPC	781810560228
UPC 12 Digit	7818105602288

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10092588](#)
- [Specifications - BYNA49RT15HHT](#)