



BYNA56R15HHT, Single Pad Compression Deadend, includes Hardware, 15 Degree NEMA Tap Pad, for ACSS



By Burndy
Catalog # [BYNA56R15HHT](#)

BURNDY; HYLUG; BYNA-R-HHT, Kit; Features: Single pad Full tension compression deadend for 250 Deg C rated ACSS transmission lines up to and including 230kV; Standard 15 Deg NEMA tap pad provides either 0 Deg or 30 Deg tap when BYNA-R15 terminal is used; with Hardware; For ACSS Conductor; RoHS Under Investigation.

General

Catalog Number	BYNA56R15HHT
Connector Type	Terminal
UPC	781810511909
UPC 12 Digit	7818105119099

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	UI
Status	

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10113639](#)
- [Specifications - BYN56R15HHT](#)