



BYNAS32RT15HT, Compression Terminal, 15 Degree Pad, 300 kcmil ACSS, High Temperature



By Burndy
Catalog # [BYNAS32RT15HT](#)

HYLUG™ Compression Terminal; 15 Degree Pad; Hi-Temp;
Accommodates: 300 kcmil (26/7) ACSS; Overlap Crimps; Die
Index: 717.

General

Catalog Number	BYNAS32RT15HT
Connector Type	Terminal
Trade Name	HYLUG™
UPC	781810500507
UPC 12 Digit	7818105005077

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

Product Assets

- [3D Models - BYNAS32RT15HT_MODEL-PDF](#)
- [3D Models - BYNAS32RT15HT_MODEL-STEP](#)
- [3D Models - BYNAS32RT15HT_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - BYNAS32RT15HT](#)