



BYNS43RHT, Jumper Loop Sleeve, Pre-filled with Joint Compound, Capped, for ACSS Conductor

By Burndy
Catalog # [BYNS43RHT](#)

Jumper Loop sleeve for 250 Deg C ACSS transmission lines at 230 kV and over; Sleeve is pre-filled with PENETROX joint compound and capped; For ACSS Conductor; RoHS Under Investigation.



General

Catalog Number	BYNS43RHT
Connector Type	Tap
Die Index	724
UPC	781810510964
UPC 12 Digit	7818105109644

Dimensions

Dimension - Length Overall inch	19.74 in
Dimension - Outside Diameter inch	1.61 in

Conductor Related

Conductor - ACSS Str Size	605 (24/7) kcmil;605 (26/7) kcmil;636 (24/7) kcmil;636 (26/7) kcmil;666.6 (24/7) kcmil
Conductor - ACSS Str Size Range	605 (24/7) kcmil-666.6 (24/7) kcmil

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50025278](#)
[Specifications - BYNS43RHT](#)



A Hubbell brand