



# BYNS49RHT, Jumper Loop Sleeve, Pre-filled with Joint Compound, Capped, for ACSS Conductor

By Burndy  
Catalog # [BYNS49RHT](#)



BURNDY; SLEEVE; BYNS-RHT; Features: Jumper Loop sleeve for 250 Deg C ACSS transmission lines at 230 kV and over; Sleeve is pre-filled with PENETROX joint compound and capped; For ACSS Conductor; RoHS Under Investigation.

## General

Connector Type	Splice
UPC	781810507186
UPC 12 Digit	7818105071866

## Dimensions

Dimension - Length Overall inch	18.70 in
---------------------------------	----------

## Conductor Related

Conductor - ACSS Str Size	900 (45/7) kcmil;900 (54/7) kcmil;954 (42/7) kcmil;954 (20/7) kcmil;954 (45/7) kcmil;954 (48/7) kcmil;954 (24/7) kcmil;954 (54/7) kcmil;954 (30/19) kcmil;1033.5 (42/7) kcmil;1033.5 (45/7) kcmil;1033.5 (48/7) kcmil;1033.5 (54/7) kcmil;1113 (42/7) kcmil;1113 (45/7) kcmil
Conductor - ACSS Str Size Range	900 (45/7) kcmil-1113 (45/7) kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	UI
Status	

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.