



C11B, Cast Bronze Ground Clamp, Cable to Water Pipe or Tube

By Burndy
Catalog # [C11B](#)

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper
Tube, 10 - 2 AWG, 1/2"- 1" Water Pipe.



Application

For Bare Wire, Connecting Grounding Conductor To Water Pipe Or Copper Tube

General

Catalog Number	C11B
EU RoHS Indicator	Yes
Material	Bronze Alloy
Material - Hardware	Brass
Plated	Y
Plating Type	Zinc Plated
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810142363
UPC 12 Digit	7818101423633

Dimensions

Dimension - Height inch	1.81 in
Dimension - Hole Size inch	0.31 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	57 mm
Dimension - Length Overall inch	2.25 in
Dimension - Pad Width inch	0.63 in
Dimension - Width inch	0.63 in
Dimension - Width mm	16 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CN_LineArt](#)
[Sales Drawings - sc210654-01](#)
[Specifications - C11B](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-C11B-SPEC-EN | REV 8/2024