



C11D, Cast Bronze Ground Clamp, Cable to Water Pipe, Tube or Rebar

By Burndy
Catalog # C11D

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1/2"- 1" Water Pipe, #4 - #8 Rebar.



Application

For Bare Wire, Connecting Grounding Conductor To Water Pipe Or Copper Tube, Direct Burial Applications In Earth And Concrete

General

Catalog Number	C11D
EU RoHS Indicator	Yes
Material	Bronze Alloy
Material - Hardware Plated	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810142349
UPC 12 Digit	7818101423499

Dimensions

Dimension - Height inch	1.81 in
Dimension - Hole Size inch	0.31 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	57 mm
Dimension - Length Overall inch	2.25 in
Dimension - Pad Width inch	0.63 in
Dimension - Width inch	0.63 in
Dimension - Width mm	16 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Rebar Size	4 ;5 ;6 ;7 ;8
Conductor - Rebar Size Range	4 -8

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

3D Models - C11D_MODEL-STEP

3D Models - C11D_MODEL-PDF

3D Models - C11D_MODEL-IGES

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_CN_LineArt

Sales Drawings - sc210654-01

Specifications - C11D



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-C11D-SPEC-EN | REV 8/2024