



C11K16D, Cast Bronze Ground Clamp for Water Pipe, Rebar, Ground Rod, to Tap Conductor

By Burndy
Catalog # C11K16D



Cast Bronze Ground Clamps, Water Pipe-1/2 " - 1 "(13 -25) (Run), Rebar-#4 -#6 (Run), Ground Rod -3/8"-1" (Run), Ground-#10-#2 Str. (Tap).

Application

For Connecting Grounding Conductor To Water Pipe, Copper Tube, Ground Rod Or Rebar, Direct Burial Applications

General

EU RoHS Indicator	Yes
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810358641
UPC 12 Digit	7818103586411

Dimensions

Dimension - Height inch	1.64 in
Dimension - L Length Overall mm	58 mm
Dimension - Length Overall inch	2.28 in
Dimension - Width inch	0.66 in
Dimension - Width mm	17 mm

Conductor Related

Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Rebar Size	4 ;5 ;6
Conductor - Rebar Size Range	4 -6
Conductor - Rod Size	3/8 in;1/2 in;5/8 in;3/4 in;7/8 in;1 in
Conductor - Rod Size Range	3/8 in-1 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - C11K16D_MODEL-STEP](#)
- [3D Models - C11K16D_MODEL-PDF](#)
- [3D Models - C11K16D_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_C11K16D_LineArt](#)
- [Sales Drawings - 10037615](#)



A proud member of the Hubbell Family.

