

# C22HD4/ODB, Cast Bronze Ground Clamp for Water Pipe to Tap Conductor

By Burndy  
Catalog # [C22HD4/ODB](#)



Cast Bronze Ground Clamps, 3.60 in L, 1-1/4"- 2" Water Pipe (Run), #8 - 4/0 Ground (Tap).

## General

Application	For Connecting Grounding Conductor, EMT Or Rigid Conduit To Water Pipe, Copper Tube, Ground Rod Or Rebar And Direct Burial
Catalog Number	C22HD4/ODB
EU RoHS Indicator	Yes
Installation Torque	50 LBS/in
Recommended in-lb	
Material	Bronze Alloy
Material - Hardware Plated	Zinc Plated Steel
Plating Type	N
Sub Brand	Zinc
Type	CLAMP
	WaterPipe Grounding Connectors
UPC	781810353196
UPC 12 Digit	7818103531966

## Dimensions

Dimension - Height fraction	2.888888888888889 in
Dimension - Height inch	2.89 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.65 in
Dimension - Width inch	1.41 in
Dimension - Width mm	36 mm

## Conductor Related

Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	8 AWG - 4/0 AWG
Conductor - Pipe EMT Size	1 1/4 in;1 1/2 in;2 in
Conductor - Pipe EMT Size Range	1 1/4 -2

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_C11HD4\\_LineArt](#)
- [Sales Drawings - SC210668-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-C22HD40DB-SPEC-EN | REV 6/2024