



C22JA, Cast Bronze Clamp, Armored Cable to Water Pipe

By Burndy
Catalog # [C22JA](#)

Cast Bronze Clamp, Armored Cable to Water Pipe, 10 AWG - 6 AWG, 1-1/4" - 2" Water Pipe.

General

Catalog Number	C22JA
Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Unplated
UPC	781810142127
UPC 12 Digit	7818101421277

Dimensions

Dimension - Height inch	2.60 in
Dimension - Height mm	66 mm
Dimension - L Length Overall mm	94 mm
Dimension - Length Overall inch	3.69 in
Dimension - Width inch	1.41 in
Dimension - Width mm	36 mm

Conductor Related

Conductor - Armored Cable Size	Y
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Size Range	10 AWG-6 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG
Conductor - Copper Str Size Range	8 AWG - 6 AWG
Conductor - Pipe EMT Size	1 1/4 in;1 1/2 in;2 in

Conductor - Pipe EMT Size Range	1 1/4 in-2 in
Conductor Type	<ul style="list-style-type: none">• Pipe EMT-Size• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CJA_LineArt](#)
- [Sales Drawings - SC210668-01](#)
- [Specifications - C22JA](#)