



C22LH1, Cast Bronze Clamp, Cable to Water Pipe to Water Pipe

By Burndy
Catalog # [C22LH1](#)



Cast Bronze Clamp, Cable to Water Pipe, 10 AWG -6 AWG, 1-1/4" - 2" Water Pipe, 1/2" hub.

General

| | |
|---------------------|-------------------|
| Material | Bronze Alloy |
| Material - Hardware | Zinc Plated Steel |
| Plated | N |
| Plating Type | Unplated |
| UPC | 781810142172 |
| UPC 12 Digit | 7818101421722 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 2.88 in |
| Dimension - L Length Overall mm | 89 mm |
| Dimension - Length Overall inch | 3.50 in |
| Dimension - Pad Width inch | 1.34 in |
| Dimension - Width inch | 0.69 in |
| Dimension - Width mm | 18 mm |

Conductor Related

| | |
|-------------------------------------|--------------------------------|
| Conductor - Armored Cable Size | N |
| Conductor - Copper Solid Size | 10 AWG |
| Conductor - Copper Solid Size Range | 10 AWG |
| Conductor - Copper Str Size | 10 AWG;9 AWG;8 AWG;7 AWG;6 AWG |
| Conductor - Copper Str Size Range | 10 AWG - 6 AWG |
| Conductor - Pipe EMT Size | 1 1/4 in;1 1/2 in;2 in |
| Conductor - Pipe EMT Size Range | 1 1/4 in-2 in |

Certifications And Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | NC |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sc210670-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-C22LH1-SPEC-EN | REV 5/2024