



C4, Cast Bronze Ground Clamp, Cable to Water Pipe or Tube

By Burndy
Catalog # C4

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 2-1/2" - 4" Water Pipe.



Application

For Bare Wire, Connecting Grounding Conductor To Water Pipe Or Copper Tube

General

| | |
|----------------------------|------------------------|
| Catalog Number | C4 |
| EU RoHS Indicator | Yes |
| Material | Bronze Alloy |
| Material - Hardware Plated | DURIUM™ Silicon Bronze |
| Plating Type | N |
| Sub Brand | Unplated |
| Trade Name | CLAMP |
| Type | N |
| UPC | Ground Clamp |
| UPC 12 Digit | 781810142325 |
| | 7818101423255 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 4.13 in |
| Dimension - Hole Size inch | 0.31 in |
| Dimension - Hole Size mm | 8 mm |
| Dimension - L Length Overall mm | 159 mm |
| Dimension - Length Overall inch | 6.25 in |
| Dimension - Pad Width inch | 1.88 in |
| Dimension - Thread Size | - |
| Dimension - Width inch | 0.96 in |
| Dimension - Width mm | 24 mm |

Conductor Related

| | |
|-------------------------------------|--|
| Conductor - Armored Cable Size | N |
| Conductor - Copper Solid Size Range | 10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG |
| Conductor - Copper Str Size Range | 10 AWG-2 AWG |
| Conductor - Copper Str Size Range | 10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG |
| Conductor - Copper Str Size Range | 10 AWG - 2 AWG |
| Conductor - Pipe EMT Size Range | 2 1/2 in;3 in;3 1/2 in;4 in |
| Conductor - Pipe EMT Size Range | 2 1/2 in-4 in |
| Conductor - Rebar Size Range | N/A |

Certifications And Compliance

| | |
|---|-------|
| Buy American Compliant | No |
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | N |
| Certification - UL Recognized | N |
| Certification - cULus | N |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | NC |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[3D Models - C4_MODEL-PDF](#)

[3D Models - C4_MODEL-STEP](#)

[3D Models - C4_MODEL-IGES](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_CN_LineArt](#)

[Sales Drawings - 10087199](#)

[Specifications - C4](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-C4-SPEC-EN | REV 8/2024