



## C4Y4/OL8D12G1SV Flexible Copper Braid

By Burndy

Catalog # [C4Y4/OL8D12G1SV](#)

Silver Plated Ferrules.

### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number C4Y4/OL8D12G1SV  
Material Copper  
UPC 621945467262

### Dimensions



Dimension - L Length Overall	206 mm
mm	
Dimension - Length Overall	8.12 in
inch	
Length	8.12 in
Width	2 in

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

### Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	1440

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50072041](#)  
[Specifications - C4Y4/OL8D12G1SV](#)  
[Specifications - BURNDY\\_C4Y4OL8D12G1SV\\_Specsheet](#)