



# PLASTIC LASHING STRAP, 50 ft REEL

By Burndy  
Catalog # [C50PLLC](#)

Lashing straps used in conjunction with CBPLLC buckles and spacers to secure communications cable to messenger strand. 250 lb tensile strength, standardly used in 24"-27" lengths for approximate 6-8" bundle diameter.

### Features

- Loop strength 250 lbs.
- UV resistant and halogen free
- Use PSC2170130 strap tensioning tool for tensioning and cutting excess strap material

### Application

- For use on Messenger Cables
- Also for use on Torque Tube

### General

Catalog Number	C50PLLC
Material	Acetal
Operating Temperature Range Celcius	-40 C to +85C
Size	50 Foot Reel
UPC	096359657064



### Dimensions

Dimensions	50 foot reel / 600 in x 8.500 in x 0.875 in
Height	0.875 in
Length	50 foot reel / 600 in
Weight	1 lb
Width	8.5 in

### Logistics

Carton Quantity	10
Pallet Quantity	1000

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - C550B150PLLC](#)  
[Sell Sheets - UNIRAP™ Plastic Lashing Strap](#)  
[Specifications - C50PLLC](#)



A Hubbell brand