



C6Y4/OL24D50G4W Rope Lay Braid

By Burndy
Catalog # [C6Y4/OL24D50G4W](#)

Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	C6Y4/OL24D50G4W
Connector Type	Braid
Material	Copper
UPC	781810668054
UPC 12 Digit	7818106680544

Dimensions

Dimension - L Length Overall	622 mm
mm	
Dimension - Length Overall	24.50 in
inch	
Length	24.5 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	24
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50039077](#)
- [Specifications - C6Y4/OL24D50G4W](#)
- [Specifications - BURNDY_C6Y4OL24D50G4W_Specsheet](#)