



CB24G72G2TN Flexible Copper Covered Braid

By Burndy
Catalog # [CB24G72G2TN](#)

Flexible Copper Covered Braid.



General

Catalog Number	CB24G72G2TN
Connector Type	Braid
Insulation	Y
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	8
Plated	Y
UPC	781810469354
UPC 12 Digit	7818104693544

Dimensions

Dimension - L Length Overall mm	1829 mm
Dimension - Length Overall inch	72.00 in
Length	72 in

Electrical Ratings

Rating - Outdoor Amperage	2000
---------------------------	------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - CB24G72G2TN_MODEL-PDF](#)
[3D Models - CB24G72G2TN_MODEL-STEP](#)
[3D Models - CB24G72G2TN_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10089447](#)



A proud member of the Hubbell Family.