



## CB4E13D62G6TN Flexible Copper Covered Braid

By Burndy  
Catalog # [CB4E13D62G6TN](#)

Flexible Copper Covered Braid.



### General

Connector Type	Braid
Insulation	Y
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810353561
UPC 12 Digit	7818103535611

### Dimensions

Dimension - L Length Overall mm	346 mm
Dimension - Length Overall inch	13.62 in
Length	13.62 in

### Electrical Ratings

Rating - Outdoor Amperage	800
---------------------------	-----

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 10034684](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-CB4E13D62G6TN-SPEC-EN | REV 5/2024